

Link to the product: <https://sforne.com/addicted-toys-travel-cleaner-silicone-model-4-p-14656.html>



ADDICTED TOYS - TRAVEL CLEANER SILICONE MODEL 4

Price	24.52 Euro
Number	81623148
Producer code	FETISHID-242886
EAN	8435565957063

Product description

The Addicted Toys Model 4 Travel Cleaner is a great option for those looking to keep their sex toys completely sanitized while traveling or away from home. With a compact and practical design, this cleaner ensures fast and effective cleaning, guaranteeing a safe and pleasant user experience.

Travel Cleaner Model 4 Features:

- Overall height: 230 mm, perfect size for easy and comfortable handling.
- Insertable length: 135 mm, allowing you to adequately reach the inside of toys for a thorough cleaning.
- Height of the bulb: 100 mm, designed for an ergonomic grip that makes it easy to use without effort.
- Thickness of the bulb: 65 mm, providing an adequate volume to contain the cleaning liquid in a safe way. efficient.
- Introduction thickness (Inf): 30 mm, Introduction thickness (Int): 29 mm, Introduction thickness (Sup): 20 mm, providing a controlled flow of liquid for effective cleaning.
- Capacity: 160 ml, a perfect amount for multiple uses, ideal to carry in your luggage without taking up too much space.

Material and Design:

This cleaner is made of durable and resistant materials, which allow an effective application of the liquid without spills or losses. Its ergonomic design ensures a comfortable and efficient experience during use, while its 160 ml capacity makes it suitable for various uses during your travels.

Use and Benefits:

The Model 4 Travel Cleaner is designed for those who want to keep their sex toys free of bacteria while away from home. With its compact size and ease of use, it is perfect for those who travel frequently or simply need a practical solution to keep their toys hygienic.

Recommendations:

To ensure that your toys stay in optimal condition, use the cleaner after each use. Apply the liquid evenly over the toy and be sure to follow the manufacturer's instructions for use for best results.