

Link to the product: <https://sforne.com/lelo-ida-wave-coral-couples-massager-p-5315.html>



## LELO - IDA WAVE CORAL COUPLES MASSAGER

|               |                        |
|---------------|------------------------|
| Price         | <b>273.35 Euro</b>     |
| Number        | <b>70138157</b>        |
| Producer code | <b>FETISHID-232090</b> |
| EAN           | <b>7350075028670</b>   |

### Product description

#### SENSUAL INDEPENDENCE

IDA™ Wave is a massager connected to an application and with two separate motors that will allow you to reach orgasm gradually. The insertable part rotates and, thanks to WaveMotion™ technology, also simulates the movement of the fingers to bring you overwhelming pleasure to the G-Spot. The upper part is larger and provides exquisite vibrations on the clitoris.

- **DOUBLE THE POWER** Two motors with powerful vibrations that offer internal and external stimulation.
- **GREATER RANGE OF INTENSITIES** Experience different levels of satisfaction with 10 intense pleasure modes.
- **APP CONTROLLED** Connect and control your device via Bluetooth for more pleasure.
- **WAVEMOTION™ TECHNOLOGY** Enjoy a perfect finger massage to stimulate your G-Spot.

#### HOW TO USE TIANI™ HARMONY

\* Before first use, charge your IDA™ Wave for 2 hours.

- **HOW TO USE THE PRODUCT WITHOUT THE APP**
  - Press the button to turn it on.
  - The LEDs will flash showing the battery charge level.
  - When the LEDs stop flashing, they will show the vibration level.
  - Press the button to change modes. They are set to 100% intensity.
  - Press the center button for 3 seconds to turn it off.
- **HOW TO USE THE PRODUCT WITH THE APP**
  - Press the center button for 3 seconds to turn it on while activating Bluetooth.
  - All LEDs will flash simultaneously to show that you are connecting with Bluetooth.
  - Open the TIANI™ Harmony app and, once you have received the confirmation message, press the center button to confirm.
  - When the LEDs shine without flickering, the device has been successfully connected.
  - In case the connection fails, the product will automatically turn off after 30 seconds.
  - Battery and vibration levels can be viewed in the app.

#### CHARACTERISTICS

- **Materials:** Biocompatible silicone and ABS
- **Size:** 63 x 56 x 93mm
- **Weight:** 102g
- **Battery:** Li-ion 3.7 V 520 mAh
- **Charge:** 2 hours at 5.0 V 200 mA
- **Use time:** Up to 2 hours
- **Standby:** Up to 90 days
- **Frequency:** 130Hz

- 
- Reducer motor frequency: 1.4 Hz
  - Interface: 1 button
  - Modes: 4 (default), up to 10 can be set via app