

Link to the product: <https://sforne.com/lelo-ida-wave-couples-massager-black-p-5314.html>

LELO - IDA WAVE COUPLES MASSAGER BLACK



Price	236.77 £
Number	70138156
Producer code	FETISHID-232089
EAN	7350075028663

Product description

SENSUAL INDEPENDENCE

IDA™ Wave is a massager connected to an application and with two separate motors that will allow you to reach orgasm gradually. The insertable part rotates and, thanks to WaveMotion™ technology, also simulates the movement of the fingers to bring you overwhelming pleasure to the G-Spot. The upper part is larger and provides exquisite vibrations on the clitoris.

- **DOUBLE THE POWER** Two motors with powerful vibrations that offer internal and external stimulation.
- **GREATER RANGE OF INTENSITIES** Experience different levels of satisfaction with 10 intense pleasure modes.
- **APP CONTROLLED** Connect and control your device via Bluetooth for more pleasure.
- **WAVEMOTION™ TECHNOLOGY** Enjoy a perfect finger massage to stimulate your G-Spot.

HOW TO USE TIANI™ HARMONY

* Before first use, charge your IDA™ Wave for 2 hours.

- **HOW TO USE THE PRODUCT WITHOUT THE APP**
 - Press the button to turn it on.
 - The LEDs will flash showing the battery charge level.
 - When the LEDs stop flashing, they will show the vibration level.
 - Press the button to change modes. They are set to 100% intensity.
 - Press the center button for 3 seconds to turn it off.
- **HOW TO USE THE PRODUCT WITH THE APP**
 - Press the center button for 3 seconds to turn it on while activating Bluetooth.
 - All LEDs will flash simultaneously to show that you are connecting with Bluetooth.
 - Open the TIANI™ Harmony app and, once you have received the confirmation message, press the center button to confirm.
 - When the LEDs shine without flickering, the device has been successfully connected.
 - In case the connection fails, the product will automatically turn off after 30 seconds.
 - Battery and vibration levels can be viewed in the app.

CHARACTERISTICS

- **Materials:** Biocompatible silicone and ABS
- **Size:** 63 x 56 x 93mm
- **Weight:** 102g
- **Battery:** Li-ion 3.7 V 520 mAh
- **Charge:** 2 hours at 5.0 V 200 mA
- **Use time:** Up to 2 hours
- **Standby:** Up to 90 days
- **Frequency:** 130Hz

-
- Reducer motor frequency: 1.4 Hz
 - Interface: 1 button
 - Modes: 4 (default), up to 10 can be set via app